

**345 Series Shock-Safe Panel Mount Enclosed Fuse Holders**



**Product Characteristics**

<b>Compatible Fuses</b>	For 3AB, 3AG, 5x20mm, or 2AG Fuses
<b>Description</b>	Designed to eliminate the possibility of electrical shock, as defined in IEC standards 60127-6. The universal fuseholder body will accept 3AB, 3AG, 5 x 20mm, and 2AG fuse sizes depending on knob selected. Permits inventory reduction of bodies and provides knob interchange versatility. Anti-tease feature eliminates circuit interruption when knob is accidentally depressed. Five fuseholder types assure design flexibility. Available with two knob styles — screwdriver slot or fingerrip. Available in two terminal styles — dual-purpose for soldering or 3/16" NEMA quick connect; and ¼" NEMA/DIN quick connect. Quick fuse size identification is provided with letters on fingerrip knob and color-coded screwdriver slot knobs.
<b>Electrical</b>	Insulation Resistance: 10,000 megohm minimum at 500 VDC. Contact Resistance: Less than .005 ohm average at currents up to 1 ampere.
<b>Mounting</b>	Threaded styles withstand 15 in.-lb. mounting torque. Low profile and High profile panel thickness: .032" min./,310" max. Quick mount panel thickness: .012" min./,360" max. Rear mount panel thickness: .012" min./,260" max.
<b>Molded Parts</b>	Body Material: Black glass-filled thermoplastic (UL 94V0).
<b>Knob Material</b>	Grey, blue or black glass-filled thermoplastic (UL94 V-0) Hex Nut Material: Black glass-filled thermoplastic.
<b>Knob</b>	Finger-Grip, Fuse Extractor type or Screwdriver Slot, Fuse Extractor type with plated copper alloy insert. Plated copper alloy contact clips. Spring loaded, locking mechanism provides an anti-tease feature and will not vibrate loose.
<b>Terminals</b>	Copper alloy. Tin-plated. Three styles available. A .187" dual purpose terminal accepts wire for soldering or a Quick-Connect receptacle. .187" terminal for NEMA Quick-Connect and .250" terminal for NEMA/DIN Quick-Connect available.
<b>Ambient Temperature</b>	-40°C to +85°C.
<b>Hardware</b>	Threaded style fuseholders are supplied with a thermoplastic hex nut unassembled. Quick mount style fuseholders are supplied with a push-on type retaining nut, black oxide finish, unassembled. A synthetic rubber "O" ring will be supplied only with the screwdriver slot knob when the drip-proof version is requested. To order with a metal internal tooth lockwasher (L) and/or neoprene panel washer (N) and/or drip-proof synthetic rubber "O" ring with Neoprene washer (NP) [Screwdriver slot knob only], add the appropriate suffix (L, N, or NP) respectively (or in combination) to the catalog number. Accessories can be order by separately.

\* Please refer to Fuseology section for information on proper fuseholder re-rating.

**Additional Information**



Datasheet



Resources




Samples

**Agency Approval**

Agency	Agency File Number	3AG/AB	5x20mm	2AG
	E14721	20A 250V	20A 250V	10A 250V
	7316	20A 250V	20A 250V	10A 250V
	40001642	10A 250V	10A 250V	—

### Dimensions



### Ordering Part Numbering System to order complete fuse holder (body and knob)

**Example 03453LS7HXLNP** - A 345 Series fuse holder for 3AG fuses with low profile body and a Screwdriver Slot knob, with 1/4" (Rt. Angle) Nema/Din QC terminals.

Series Name ← 0 345 3 LS 7 H X L N P

Fuse Size	Style	Terminals	Packing	Accessory*
2	LF	1	H	L
2AG .177" x .570"	Low Profile Body Black Fingergrasp Knob	3/16" (Rt. Angle) Dual Purpose Solder/QC	For 100 Pieces (Bulk)	Lockwasher
3	RF	2		N
3AG .250" x 1.250"	Rear Mount Body Black Fingergrasp Knob	3/16" (Straight) Dual Purpose Solder/QC	Neoprene Washer	
5	HS	3	P	Drip-Proof "O" Ring** with Neoprene Washer
5 x 20mm .197" x .787"	High Profile Body Screwdriver Slot Knob	3/16" (Rt. Angle) NEMA QC	*Optional (L,N,P) can be ordered individually or in combination **Screwdriver slot knob only	
	LS	4		
	Low Profile Body Screwdriver Slot Knob	3/16" (Straight) NEMA QC		
	QS	7		
	Quick Mount Body Screwdriver Slot Knob	1/4" (Rt. Angle) NEMA/DIN QC		
	Screwdriver Slot Knob	8		
	2AG - Blue Knob	1/4" (Straight) NEMA/DIN QC		
	3AG - Grey Knob 5 x 20mm - Black Knob			

Note - If accessory is needed, add the "X" as filler on the ordering part number

### To Order Body Including Nut(s) Only

Terminal Style	Bottom Terminal	Low Profile Body Part Number***	High Profile Body Part Number	Rear Mount Body Part Number	Quick Mount Body Part Number
3/16" Dual Purpose	(Rt. Angle)	03453LF1ZX010	03453HS1ZX010	03453RF1ZX010	03453QS1ZX010
3/16" Dual Purpose	(Straight)	03453LF2ZX010	03453HS2ZX010	03453RF2ZX010	03453QS2ZX010
3/16" NEMA QC	(Rt. Angle)	03453LF3ZX010	03453HS3ZX010	03453RF3ZX010	03453QS3ZX010
3/16" NEMA QC	(Straight)	03453LF4ZX010	03453HS4ZX010	03453RF4ZX010	03453QS4ZX010
¼" NEMA/DIN QC	(Rt. Angle)	03453LF7ZX010	03453HS7ZX010	03453RF7ZX010	03453QS7ZX010
¼" NEMA/DIN QC	(Straight)	03453LF8ZX010	03453HS8ZX010	03453RF8ZX010	03453QS8ZX010

\*\*\*Low Profile Body will accept either Fingergrip or Screwdriver Slot Knob.  
 Z - 100 pieces (Bulk)  
 X - Filler

### To Order Knob Only

Fuse Size	Fingergrip Knob	Screwdriver Slot Knob
2AG	03452LF1HX020	03452LS1HX020
3AG	03453LF1HX020	03453LS1HX020
5 × 20mm	03455LF1HX020	03455LS1HX020

H - 100 Pieces (Bulk)  
 X - Filler

### To Order Accesories Only

Accessory	Packaging	Part Number
ACS Rubber Washer	Bulk (100 pieces)	09010002H
ACS Nut	Bulk (100 pieces)	09030097H
ACS Lockwasher	Bulk (100 pieces)	09050023H
ACS O-Ring	Bulk (100 pieces)	09010134H

H - 100 Pieces (Bulk)