



SP03A-3.3 Series 3.3V 150A Diode Array


OBSOLETE DATE: 2016 PCN/ECN# N/A
REPLACED BY: LC03-3.3BTG TVS Diode Array



Pinout



Functional Block Diagram



Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

Description

This SP03A provides overvoltage protection for applications such as 10/100/1000 BaseT Ethernet, and T3/E3 interfaces. This new protector combines the TVS diode element with a diode rectifier bridge to provide both longitudinal and differential protection in one package. This design results in a capacitive loading characteristic that is log-linear with respect to the signal voltage across the device. This reduces intermodulation (IM) distortion caused by a typical solid-state protection solution. The application schematic provides the connection information and the SP03A is rated for GR-1089, intra-building transient immunity requirements for telecommunication installations.


Features

- Lightning Protection, IEC 61000-4-5 2nd edition, 150A ($t_P=8/20\mu s$)
- EFT, IEC 61000-4-4, 40A ($t_P=5/50ns$)
- Low insertion loss, log-linear capacitance
- Low clamping voltage
- SOIC-8 surface mount package (JEDEC MS-012)
- Combined longitudinal and metallic protection
- Clamping speed of nanoseconds
- UL V-0 Flammability epoxy molding
- RoHS compliant and lead-free

Applications

- T1/E1 Line cards
- T3/E3 and DS3 Interfaces
- STS-1 Interfaces
- 10/100/1000 BaseT Ethernet

Application Example



This schematic shows a high-speed data interface protection solution. The SP03A-3.3BTG is compatible with the intra-building surge requirements of Telcordia's GR-1089-CORE, and the Basic Level Recommendations of ITU K.20 and K.21. The TeleLink fuse provides overcurrent protection for the long term 50/60 Hz power fault events.

OBSOLETE DATE: 2016 PCN/ECN# N/A
REPLACED BY: LC03-3.3BTG TVS Diode Array

Absolute Maximum Ratings

| Parameter | Rating | Units |
|---|--------|-------|
| Peak Pulse Current (8/20μs) | 150 | A |
| Peak Pulse Power (8/20μs) | 3300 | W |
| IEC 61000-4-2, Direct Discharge, (Level 4) | 30 | kV |
| IEC 61000-4-2, Air Discharge, (Level 4) | 30 | kV |
| IEC 61000-4-5 (8/20μs) | 150 | A |
| Telcordia GR 1089 (Intra-Building) (2/10μs) | 100 | A |
| ITU K.20 (5/310μs) | 40 | A |

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Thermal Information

| Parameter | Rating | Units |
|---|------------|-------|
| SOIC Package | 170 | °C/W |
| Operating Temperature Range | -40 to 125 | °C |
| Storage Temperature Range | -55 to 150 | °C |
| Maximum Junction Temperature | 150 | °C |
| Maximum Lead Temperature (Soldering 20-40s) (SOIC - Lead Tips Only) | 260 | °C |

Electrical Characteristics (T_{OP} = 25°C)

| Parameter | Symbol | Test Conditions | Min | Typ | Max | Units |
|---------------------------------|------------------|---|-----|------|-----|-------|
| Reverse Stand-Off Voltage | V _{RWM} | I _T ≤ 1μA | - | - | 3.3 | V |
| Reverse Breakdown Voltage | V _{BR} | I _T = 2μA | 3.3 | - | - | V |
| Snap Back Voltage | V _{SB} | I _T = 50mA | 3.3 | - | - | V |
| Reverse Leakage Current | I _R | V _{RWM} = 3.3V, T = 25°C | - | - | 1 | μA |
| Clamping Voltage, Line-Ground | V _C | I _{PP} = 50A, t _p = 8/20 μs | - | - | 13 | V |
| Clamping Voltage, Line-Ground | V _C | I _{PP} = 100A, t _p = 8/20 μs | - | - | 17 | V |
| Dynamic Resistance, Line-Ground | R _{DYN} | (V _{C2} - V _{C1}) / (I _{PP2} - I _{PP1}) | - | 0.15 | - | Ω |
| Clamping Voltage, Line-Line | V _C | I _{PP} = 50A, t _p = 8/20 μs | - | - | 15 | V |
| Clamping Voltage, Line-Line | V _C | I _{PP} = 100A, t _p = 8/20 μs | - | - | 20 | V |
| Dynamic Resistance, Line-Line | R _{DYN} | (V _{C2} - V _{C1}) / (I _{PP2} - I _{PP1}) | - | 0.25 | - | Ω |
| Junction Capacitance | C _j | Between I/O Pins and Ground V _R = 0V, f = 1MHz | - | 9 | 12 | pF |
| | | Between I/O Pins V _R = 0V, f = 1MHz | - | 4.5 | 6 | pF |

Figure 1: Non-repetitive Peak Pulse Current vs. Pulse Time





Figure 2: Current Derating Curve



OBSOLETE DATE: 2016 PCN/ECN# N/A
REPLACED BY: LC03-3.3BTG TVS Diode Array

Figure 3: 8/20µS Pulse Waveform




Figure 4: Clamping Voltage vs. Peak Pulse Current




Figure 5: Capacitance vs. Reverse Voltage






Figure 6: Forward Voltage vs. Forward Current




Soldering Parameters

| | | |
|--|--|------------------|
| Reflow Condition | Pb – Free assembly | |
| Pre Heat | - Temperature Min (T _{s(min)}) | 150°C |
| | - Temperature Max (T _{s(max)}) | 200°C |
| | - Time (min to max) (t _s) | 60 – 180 secs |
| Average ramp up rate (Liquidus) Temp (T _L) to peak | 3°C/second max | |
| T _{S(max)} to T _L - Ramp-up Rate | 3°C/second max | |
| Reflow | - Temperature (T _L) (Liquidus) | 217°C |
| | - Temperature (t _L) | 60 – 150 seconds |
| Peak Temperature (T _p) | 260 ^{+0/-5} °C | |
| Time within 5°C of actual peak Temperature (t _p) | 20 – 40 seconds | |
| Ramp-down Rate | 6°C/second max | |
| Time 25°C to peak Temperature (T _p) | 8 minutes Max. | |
| Do not exceed | 260°C | |




OBSOLETE DATE: 2016 PCN/ECN# N/A
REPLACED BY: LC03-3.3BTG TVS Diode Array

Package Dimensions – Mechanical Drawings and Recommended Solder Pad Outline




| Package | SOIC | | | |
|-----------|-------------|------|-----------|-------|
| Pins | 8 | | | |
| JEDEC | MS-012 | | | |
| | Millimetres | | Inches | |
| | Min | Max | Min | Max |
| A | 1.35 | 1.75 | 0.053 | 0.069 |
| A1 | 0.10 | 0.25 | 0.004 | 0.010 |
| A2 | 1.25 | 1.65 | 0.050 | 0.065 |
| B | 0.31 | 0.51 | 0.012 | 0.020 |
| c | 0.17 | 0.25 | 0.007 | 0.010 |
| D | 4.80 | 5.00 | 0.189 | 0.197 |
| E | 5.80 | 6.20 | 0.228 | 0.244 |
| E1 | 3.80 | 4.00 | 0.150 | 0.157 |
| e | 1.27 BSC | | 0.050 BSC | |
| L | 0.40 | 1.27 | 0.016 | 0.050 |

Embossed Carrier Tape & Reel Specification – SOIC Package




| | Millimetres | | Inches | |
|-------------|---------------|------|-----------------|-------|
| | Min | Max | Min | Max |
| E | 1.65 | 1.85 | 0.065 | 0.073 |
| F | 5.4 | 5.6 | 0.213 | 0.22 |
| P2 | 1.95 | 2.05 | 0.077 | 0.081 |
| D | 1.5 | 1.6 | 0.059 | 0.063 |
| D1 | 1.50 Min | | 0.059 Min | |
| P0 | 3.9 | 4.1 | 0.154 | 0.161 |
| 10P0 | 40.0 +/- 0.20 | | 1.574 +/- 0.008 | |
| W | 11.9 | 12.1 | 0.468 | 0.476 |
| P | 7.9 | 8.1 | 0.311 | 0.319 |
| A0 | 6.3 | 6.5 | 0.248 | 0.256 |
| B0 | 5.1 | 5.3 | 0.2 | 0.209 |
| K0 | 2 | 2.2 | 0.079 | 0.087 |
| t | 0.30 +/- 0.05 | | 0.012 +/- 0.002 | |

Part Numbering System



Part Marking System



Ordering Information

| Part Number | Package | Marking | Min. Order Qty. |
|--------------|------------------|-----------|-----------------|
| SP03A-3.3BTG | SOIC Tape & Reel | SP03A-3.3 | 2500 |

Product Characteristics

| | |
|---------------------------|------------------------|
| Lead Plating | Matte Tin |
| Lead Material | Copper Alloy |
| Lead Coplanarity | 0.004 inches (0.102mm) |
| Substrate material | Silicon |
| Body Material | Molded Epoxy |
| Flammability | UL 94 V-0 |

Notes :

- All dimensions are in millimeters
- Dimensions include solder plating.
- Dimensions are exclusive of mold flash & metal burr.
- Blo is facing up for mold and facing down for trim/form, i.e. reverse trim/form.
- Package surface matte finish VDI 11-13.